LUPEROX® K10N E



METHYL ETHYL KETONE PEROXIDE CAS NR: 1338-23-4 EINECS: 215-661-2

APPLICATIONS

Luperox[®] K10N E is high activity Methyl Ethyl Ketone Peroxide used for the cure of unsaturated polyester resins at room temperatures in combination with a cobalt accelerator. Luperox[®] K10N E is used for applications such as hand lay-up, spray-up etc. and thanks to its high activity is particularly suitable during the cold season. Its low viscosity makes it ideal for spray-up techniques (airless) with external mixing. Use in gel coats is possible but requires a study case by case.

SPECIFICATIONS

	Unit	Value	Method of Analysis
Physical form	-	Clear liquid	AM/I/71/A
Active oxygen	% W	9.7 – 10.0	AM/I/53/C

CARACTERISTICS

	Unit	Value
Density at 20°C	g/ml	1,144
Refractive index at 20°C	-	1,4621
Viscosity at 20°C	mPa s	15
Flash point (setapoint)	°C	79
S.A.D.T (1)	°C	60
M.S.T (2)	°C	25

- (1) Self- accelerating decomposition temperature.
- (2) Maximum Storage Temperature.

DOSAGE

Typical concentrations for Luperox® K10N E run from 1 to 3% by weight based on resin and for cobalt accelerator from 0,25% to 4% based on 1% metal content solution. Luperox® K10N E is recommended for the curing of ortho- and isophthalic resins at temperatures between 15 and 50°C

A faster reaction with shorter demold times can be obtained by the addition of promoters such as dimethyl aniline or diethyl aceto acetamide to the cobalt accelerator.



LUPEROX® K10N E

CURING PROPERTIES

The factor to be considered in selecting the optimum initiator / accelerator system are:

- 1. Process
- 2. Resin type
- 3. Required gel time or pot-life
- 4. Part thickness
- 5. Room temperature
- 6. Nature and quantity of additives
- 7. Dosage optimization between Luperox® K10N E and accelerator.

For comparison purposes, the table below shows activities of different MEKPs.

Product	Gel time	Cure time	Peak exothermic	Barcol hardness after 7 hours
Luperox® K1G E	15 minutes	34 minutes	110 °C	48-50
Luperox® K12G E	36 minutes	61 minutes	99 °C	47-51
Luperox® K10N E	12 minutes	26 minutes	124 °C	47-50

Test were carried out at 22°C in a medium activity resin following the DIN 16945 method with 2% of MEKP and 0,5% of cobalt accelerator (1% metal content solution) in a test tube of 150 x 19 mm.

STANDARD PACKAGING

25 kg drums and 4 x 5 kg drums.

SAFETY - HAZARD

Please consult the Safety Data Sheet before using the product.

STORAGE - HANDLING

Product can be stored minimum three months after receiving date, if kept in appropriate conditions and below its maximum storage temperature. Refer to the Safety Data Sheet for detailed storage instructions.

The statements, technical information and recommendations contained herein are believed to be accurate as of the date hereof. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, ARKEMA expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information; NO WARRANTY OF FITNESS FOR ANY PARTICULAR PURPOSE, WARRANTY OF MERCHANTABILITY OR ANY OTHER WARRANTY, EXPRESS OR IMPLIED, IS MADE CONCERNING THE GOODS DESCRIBED OR THE INFORMATION PROVIDED HEREIN. The information provided herein relates only to the specific product designated and may not be applicable when such product is used in combination with other materials or in any process. The user should thoroughly test any application before commercialization. Nothing contained herein constitutes a license to practice under any patent and it should not be construed as an inducement to infringe any patent and the user is advised to take appropriate steps to be sure that any proposed use of the product will not result in patent infringement.

See MSDS for Health & Safety Considerations

